

Benötigte Höhe der Sortimo Koffer / BOXXen im Globelyst M System						
	nur Artikel	auf Kofferschub KS	auf Multislide MS	auf Schienen KS	auf Schienen MBS	auf Fachboden FB
Koffer						
KM / WM / DM / DK 320	4	6	7	5	-	-
KM / WM / DM 330	6	8	9	7	-	-
KM / WM / DM 340	8	10	11	9	-	-
KM / WM / DM 350	10	12	13	11	-	-
T-Boxx	5	7	8	6	7	8
HD-Boxx	6	8	9	7	7	9
L-Boxx 102	7	9	10	8	9	10
L-Boxx 136	9	11	12	10	11	12
L-Boxx 238	15	17	18	16	17	18
L-Boxx 374	23	25	26	24	25	26
LT-Boxx 136	9	11	12	10	10	12
LT-Boxx 170	11	13	14	12	12	14
LT-Boxx 272	18	20	21	19	19	21
LT-Boxx 408	27	29	30	28	28	30
LS-Boxx 306	19	21	22	20	21	22
Bosch WLC & L-BOXX 136	11	-	-	-	-	-
i-Boxx 53	3	-	6	-	-	-

i-Boxx 72	4	-	7	-	-	-
i-Boxx-Rack 3-289	18	20	21	19	19	21
i-Boxx-Rack 5-459	28	30	31	29	29	31
S-Boxx 03-8	8	-	-	-	-	11
S-Boxx 04-9	9	-	-	-	-	12
S-Boxx 05-11	11	-	-	-	-	14
S-Boxx 04-5	5	-	-	-	-	8
M-Boxx	9	-	-	10	10	12